

HR7627
 HR7628
 HR7629




EN User manual
 DE Benutzerhandbuch

FR Mode d'emploi
 TR Kullanım kılavuzu


PHILIPS




		(MAX)	(MAX)	
		5 x 1 sec	500 g	P
		5 x 1 sec	500 g	P/2
		30 sec	50 g	P
		60 sec	250 g	2
		45 sec	250 g	2
		2-3 min	500 g	1
			360 ml	
		60-180 sec	350 ml	1
		60-180 sec	4 pcs	1
		30 sec	500 g	1
		30 sec	500 g	1
		30 sec	2 pcs	1
		30 sec	300 g	1
		30 sec	500 g	1
		30 sec	200 g	1
		30 sec	2 pcs	1
		30 sec	500 g	1
		4 min	1 kg	1
		20 sec	500 g	1
		1 min	1 L	2
		1 min	1 L	2
		1 min	1 L	2
		P x 9	6 x	P
		3 min	400 g / 600 ml	2




2 




3 




4 




5  




6 



















7 




8




9

							
	✓	✓	✗		✓	✓	✓
	✓	✓	✗		✓	✓	✗
	✓	✓	✓		✓	✓	✓
	✓	✓	✗		✗	✗	✓
	✓	✓	✗		✗	✗	✓

10



11



12

